




RotaSpray
ECO₂



In cooperation with CHT R. Beitlich GmbH

®** are trademarks from CHT

Rotating Atomizer System ROTO-FINISHER®

Silicone softener (Emulsion)

- ✓ Very soft, very typical silicone handle with high surface soothness
- ✓ Improves the sewability
- ✓ Improves the "easy care" effects in resin finishing
- ✓ Improves the elastic forces of fabric
- ✓ Low tendency to turn yellow

Application on the stenter

Spray recipe : up to 100 g/l in MA application - **ARRISTAN®* 66**, density 0,98 g/m³
use 1 g/l KOLLASOL®** CDO anti foam

Minimum application (MA) : 40 % pick-up

Drying temperature : 150°C

Contact-free (MA) minimum application of silicone softener

- ✓ Increased productivity for less energy and costs
- ✓ No impact of residues of auxiliaries on the goods to the spray liquor due to contact free application
- ✓ No more expensive and time-consuming maintenance (e.g. roller change/grinding of rubber coverings)

Closed spray chamber ROTO-FINISHER®

- ✓ Time - delayed forced application by two-time spraying the front and back side of the fabric
- ✓ The first spray point serves as a pre-wetting, thus ensuring a homogeneous penetration of the spray solution
- ✓ An air curtain and the closed spray chamber guarantees to fulfill the maximum concentration values at the workplace and will avoid „OVERSPRAY“ (= too fine micro drops)

